



Date d'édition : 09.01.2025

**Ref : 8-1004173-000-10-0**

**P 4.173 Ballasts conventionnels**

Experimental panel P 4.173 "Ballast units" offers three ballast configurations for fluorescent lamps: - 2 ballast units: 18 W - 1 ballast unit: 36 W By using the corresponding masks, only the sockets required in each case are exposed for connection to the selected ballast unit. The following experiments can be accessed: - Single-circuit, inductive, capacitive - Dual-circuit, series connection - Dimming circuitry - Two-phase circuitry Connection: via 4 mm safety sockets Operating voltage: 230 V AC, 50 ... 60 Hz Dimensions in mm: 259 x 297 x 94 (W xH X D) Weight: 2.86 kg